

physical. chemical. biological.





# P14 Rapid **Capacitive Humidity Sensor** Optimal for weather balloons and radio sondes









### Benefits & Characteristics

- Ultra fast response time
- Condensation resistant
- High humidity stability
- Wide temperature range
- Temperature shock resistant
- Fast recovery time
- Customer-specific sensor available upon request

#### Illustration<sup>1)</sup>





1) For actual size, see dimensions

#### Technical Data

	Wired	SMD
Dimensions (L x W x H / H2 in mm):	5 x 3.81 x 0.4 / 0.8	6.35 x 2.54 x 0.4
Capacitance at 30 % RH and +23 °C (C <sub>30</sub> ):*	140 pF ±40 pF	180 pF ±50 pF
Sensitivity at $C_{30} = 150 \text{ pF} / 180 \text{ pF} / (15 \% \text{ RH to } 90 \% \text{ RH})$ :	0.25 pF/% RH	0.3 pF/% RH
Operating humidity range:	0 % RH to 100 % RH (maximal dew point +85 °C)	
Operating temperature range:	-80 °C to +150 °C	
Loss factor:	< 0.01 (at 23 °C, at 10 kHz, at 90 % RH)	
Linearity error:	< 1.5 % RH (15 % RH to 90 % RH at +23 °C after one point calibration)	
Hysteresis:	< 1.5 % RH	
Response time t <sub>63</sub> : <sup>2)</sup>	< 1.5 s (50 % RH to 0 % RH at +23 °C)	
2) The response time is often measured for increasing humidity steps, whereas physics predicts that decreasing humidity leads to generally far longer response times for capacitive humidity sensors. IST thus measures response times always for decreasing humidity values, since this is the worst case.		
Temperature dependence (nominal):	$\Delta$ % RH = (B1 x % RH + B2) x T [ °C] + (B3 x % RH + B4)	
	B1 = 0.0014 [1/°C]	B2 = 0.1325 [% RH/°C]
	B3 = -0.0317	B4 = -3.0876 [% RH]
Measurement frequency:	1 kHz to 100 kHz (recommended 10 kHz)	
Maximal supply voltage:	< 12 V <sub>pp</sub> AC	



physical. chemical. biological.











Signal form: alternating signal without DC bias


CuP-SIL-wire post-plated with Sn, 10 mm or Au/Cu-wire, Ø 0.4 mm or SMD automatic assembly compatible


\* Customer-specific alternatives available

The calibration of the sensor must be done 5 days after soldering at the earliest.

#### Characteristic Curve

Connection:\*







physical. chemical. biological.











# Order Information - SIL (CuP-SIL-wire post-plated with Sn, 10 mm)

P14 Rapid (140 ±40pF) 040.00119

### Order Information - SMD

Order code

P14 SMD Rapid-G (180 ±50pF) Order code 040.00170

## Order Information - Au/Cu-wire, Ø 0.4 mm

	P14 Rapid-W (140 ±40pF)	
Order code	040.00177	



